



8255-15: One Light Outdoor Post Lantern



Collection: Polycarbonate Outdoor

Outdoor White Finish Polycarbonate Lantern Top with Clear Acrylic Beveled Panels. Non-corrosive and Rust Free.

Outdoor post lantern in white finish Polycarbonate with clear acrylic beveled panels. Non-corrosive and rust free. Fits 3" post (sold separately).

UPC #:785652825552

Finish: White (15)

Dimensions:

Length: 8" **Wire:** 6 1/2"
Width: 8" **Bulb Appearance:** Clear
Height: 18"
Weight: 1.78 lbs.

Bulbs:

1 - Medium A19 100w Max. 120v - Not included
1 - LED Medium A19 8w Max. 120v - Not included
1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Polycarbonate - White
1 Holder - Polycarbonate - White

Safety Listing:

Safety Listed for Wet Locations

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Acrylic	Clear Beveled	4									

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8255-15	1	785652825552	8.6	8.5	16.5	0.698	2.2	250	Yes
NJ Pallet		96		48	40	67.8	75.333	211.2		No
NV Pallet		100		48	40	67.8	75.333	220		No