

## DD42LED5K 42 Watt LED Dusk to Dawn







## **SPECIFICATIONS:**

**Lumens:** 3946 **Watts:** 39.20

Lumens/Watt: 100.66

**CRI:** 74.0 **CCT:** 5086

Lifespan: 50,000 hrs.

#### **Construction:**

Durable die-cast aluminum housing with powder coated gray finish. The housing is designed for greater heat dissipation which allows for lower operating temperatures which results in a brighter light, more stable color and longer LED and driver life.

## Lens:

UV stable polycarbonate lens designed to provide high efficiency, Greater footcandles and a large pattern.

#### **Driver:**

Constant current, Class 2, 120 VAC, 50-60 Hz Off-State Power – 0 Watts 0-10 V Dimming

#### LEDs:

Atlas LEDs provide higher lumen output, greater energy efficiency and more reliable fixture performance.

DD42LED5K operates at 5000K CCT

Delivers 70% or greater of initial lumens at 50,000 hours

## **Glare Free:**

Positioning of the LEDs results in the light being directed to desire locations eliminating glare and offensive light.

## Warranty:

Five-year limited warranty

### Testing:

Atlas LED luminaires have been tested by an independent laboratory in accordance with IESNA LM-79 & LM-80, and have received the Department of Energy "Lighting Facts" label.

#### **Mounting:**

Suitable for pole mount application, 1 5/8" diameter mounting arm included.

#### **Photocontrol:**

NEMA 120VAC twist lock photocontrol included.


#### Weight:

7.6 lbs.

# 



## **DIMENSIONS:**




**Patent Pending** 



## **DD42LED5K** 42 Watt LED Dusk to Dawn

## **PHOTOMETRIC**

# Recommended Mounting Height - 12-14 ft.



FOOTCANDLES ON THE GROUND							
Mtg.	90°			45°			Avg. FCs
Hgt.	5'	10'	15'	5'	10'	15'	450 sq. ft.
12'	5.3	4.4	2.2	5.1	4.1	2.2	3.9
14'	3.7	3.6	2.2	3.6	3.4	2.1	3.1

