



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192

**PART NUMBER:** 96294  
**DESCRIPTION:** 24 AWG /4 Pair Category 5e Direct Burial Data Cable  
**COMPLIANCE:**  
➤ For outdoor use only  
➤ Meets or exceeds TIA/EIA 568-C.2

## Construction Parameters:

Conductor	24 AWG Solid Bare Copper	<u>DIAMETER*</u>
Dielectric	Solid polyethylene with insulation with water blocking gel	0.020"
Assembly	Each pair has different lay length for cross-talk prevention	0.040"
Jacket	Polyethylene	0.220"

\* = Nominal value

## Product Electrical Characteristics:

Max Capacitance (nF/100m @ 1 kHz)	Max DC Resistance (Ω/100m @ 20°C)	Max Delay Skew (ns/100m)	Nom Velocity of Propagation (%)	Characteristic Impedance (Ω @ 1-100 MHz)
5.6	9.38	45	68	100 +/- 15

Freq (MHz)	Max Insertion Loss (dB/100m)	Min NEXT Loss (dB)	Min PSNEXT Loss (dB)	Min ACR (dB/100m)	Min PSACR (dB/100m)	Min ELFEXT (dB/100m)	Min PSELFEXT (dB/100m)	Min Return Loss (dB)
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25
16	8.2	47.3	44.3	39.1	36.1	39.7	36.7	25
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	25
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	21.5
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1

Pair Colors: W/BL with BL, W/OR with O, W/GR with GR, W/BR with BR  
Jacket Color: Black

Legend (Ink Print) COLEMAN CABLE 96294 CAT 5E 24/4PR DIRECT BURIAL – Z/YY (XXXX) - NNNNNN

(Also printed with sequential footage & date code)

This product complies with European Directive 2011/65/EU (RoHS-2)

On special orders, the customer will accept all mil lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control, all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Specification Issue Date: April 12, 2013