



## 8509-02: One Light Outdoor Wall Lantern



**Collection:** Classico

Outdoor Solid Brass Wall Lantern in Polished Brass Finish with Clear Beveled Glass.

Outdoor wall lantern finished in polished solid brass with clear beveled glass.

**UPC #:**785652850929

**Finish:** Polished Brass (02)

### Dimensions:

<b>Width:</b>	7"	<b>Extends:</b>	7 1/4"
<b>Height:</b>	12 1/4"	<b>Wire:</b>	6 1/2"
<b>Weight:</b>	3.3 lbs.	<b>Mounting Proc.:</b>	Cap Nuts
		<b>Connection:</b>	Mounted To Box
		<b>Bulb Appearance:</b>	Clear

### Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

### Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

- 1 Body - Brass - Polished Brass
- 1 Canopy - Brass - Polished Brass
- 1 Socket Cover - Brass - Polished Brass

### Safety Listing:

- Safety Listed for Wet Locations
- Safety Listed for Wet Locations

### Instruction Sheets:

- English (HC-231)
- French (F-009)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	6									

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5 1/2	4 3/4			3 1/4	9

### Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	8509-02	1	785652850929	8.25	8.5	14.25	0.578	4.1	125	Yes
Master Pack		2	10785652850926	19	10.5	17	1.963	10	125	Yes
NJ Pallet		92		48	40	72	80	460		No
NV Pallet		100		48	40	79.58	88.422	537		No