



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P3760-09EBWB

Melon

Two-light flush mount with alabaster glass bowl. Twist on and off glass bowl. 13 watt GU24 spiral compact fluorescent lamps included.

Category: Close-to-Ceiling

Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Etched Alabaster glass bowl



Diameter: 16-3/4"

Height: 5-1/2"

Glass: 12-7/16" dia.

Height: 4-3/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted Mounting strap for outlet box included Ceiling pan covers a standard 4" hexagonal recessed outlet box 16-5/8" dia.	Pre-wired 6" of wire supplied 120V	Quantity: 2 18W GU-24 (included) GU24 sockets	cCSAus Damp location listed 3 year warranty Companion Close-to-ceiling, fixtures are available 