

MINKA-LAVERY®

| | |
|---|--|
| Item #: 1423-84 | UPC Code: 747396044668 |
| Product Family Name: Paradox™ | Finish: BRUSHED NICKEL |
| Category: Mini Chandeliers | Category Type: Mini Chandelier |
| Certification E127416 | |
| Patents | |
| Notes: *Also available 1423-281 | |



Image File Name:
1423-84--
1377121171.jpg



MEASUREMENTS

| | | | |
|----------------------------------|-------------------------------------|-------------------------------------|----------------------------|
| Width: 23 | Length: 23 | Height: 20 | Extension: 23 |
| Height Adjustable: Yes | Min Overall Height: 23.00 | Max Overall Height: 94.00 | Slope: Yes |
| Wire Length: 120 | Chain Length: 72 | Safety Cable Included: No | Net Weight: 8.55 |
| Canopy Width: 5.00 | Canopy Height: 1.00 | Canopy Length: 6.38 | |
| Backplate Width: | Backplate Height: | Center to Top: | Center to Bottom: |

LAMPING

| | | | | |
|---------------------------------|-------------------------------|-------------------|---------------------|------------------------------|
| No. of Bulbs: 3 | Light Type: A19 Med | | | |
| Max Bulb Wattage: 100 | Socket: E26 Med | | | |
| Dimmable: Yes | Ballast: | Rated Life Hours: | Photocell Included: | Lamps Included: No |
| Lamp Included: No | Color Temp.: | CRI: | Initial Lumens: | Delivered Lumens: |

SHADE / GLASS

| | |
|---------------------------|---------------------------|
| Description: | Material: Glass |
| Part No.: G5421 | Quantity: 3 |
| Width: 6.38 | Height: 4.50 |
| | Length: 6.38 |



SHIPPING

| | | |
|---------------------------------|------------------------------------|--|
| Carton Width: 12.500 | Carton Height: 18.250 | Carton Length: 14.500 |
| Carton Weight: 12.672 | Carton Cubic Feet: 1.914 | Small Package Shippable: Yes |
| Master Pack Width: | Master Pack Height: | Master Pack Length: |
| Master Pack Weight: | Master Cubic Feet: | Multi-Pack: 1 |
| | | Master Pack: 1 |



Damp Location
Yes



Title 17
Yes



UL LISTED
Yes