

FM362BS: 3 - Light Indoor Flush Mount



Dimensions:

Diameter: 15" **Wire:** 8" (color/Black/White)
Height: 6 1/2" **Connection:** Mounted To Box
Weight: 5.28 lbs.

Bulbs:

3 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - Brushed Steel
 1 Canopy - Stamped Steel - Brushed Steel

Safety Listing:

Safety Listed for Damp Locations / IC
 Safety Listed for Damp Locations / IC

Instruction Sheets:

English (2011B)

Collection: Beckett

UPC #: 014817425680

Finish: Brushed Steel (BS)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	FM362BS	1	014817425680	17	16.75	8.25	1.359	6.5	150	Yes
Master Pack	FM362BS	4	10014817425687	34.5	17.75	17.5	6.202	29.1	150	Yes
NJ Pallet		32		48	40	74.5	82.778	232.8		No
NV Pallet		48		48	40	75	83.333	369.6		No