



Item #: F523-ABD	UPC Code: 706411045547
Product Family Name: Aluma	Finish: Brushed Aluminum
Category: Exterior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents	
Notes:	



Image File Name:
F523-ABD--
1509647399.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
ABS Construction		No	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	4	12	19.18
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
6	0.75		
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
14.00	10.75	80	153*20 mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	73		103		163
Amps:	0.28		0.37		0.47
Watts:	12.900		25.300		51.500
CFM:	2091.80		3232.60		4834.74
CFM/Watts:	162.16		127.77		93.88



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	Yes
	Included Remote Control:	Included Wall Control:
	RSC213	
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
		WCS213

LAMPING

No. of Bulbs:	Light Type:			
1	T4 E11 Mini Halogen			
Max Bulb Wattage:	Socket:			
100	E11, Mini Candleabra			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
Yes	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes				

GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
GF523-1	1
Width:	Height:
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:
11.880	10.250	24.000
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
22.020	1.691	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1



Wet Location

Yes



UL Listed

Yes