



Item #: **F688-WH**
 Product Family Name: **Kola**
 Category: **Interior Fan**
 Certification: **4000048**
 Patents
 Notes:

UPC Code: **706411044151**
 Finish: **White**
 Category Type: **Ceiling Fan**



Image File Name:
 F688-WH--
 1509648332.jpg



MEASUREMENTS

Blade Finish:		Reversible Blades:	
		No	
Blade Material:		Slope:	
Plywood Construction		No	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
52	5	12	18.17
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
6	0.75		
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
13.25	11.00	80	172x14mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	61		120		190
Amps:	0.22		0.40		0.60
Watts:	8.900		29.700		71.300
CFM:	2126.00		3689.00		6002.00
CFM/Watts	238.88		124.21		84.18



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
Yes	Yes	Yes
	Included Remote Control:	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	RCS213,WCS223	WC105,WC106,WCS213,WCS223

LAMPING

No. of Bulbs:	Light Type:			
	N/A			
Max Bulb Wattage:	Socket:			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
No	No			
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:
15.380	11.630	20.880
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
21.868	2.161	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack:
		1



ENERGY
STAR
Yes



Title 17
Yes



ETL Intertek
Yes