

Item #: 8692-66	UPC Code: 747396078779
Product Family Name: Harrison™	Finish: BLACK
Category: Wall Mount	Category Type: Wall Bracket
Certification 3187291	
Patents U.S. Patent(s): D463,062	
Notes:	



Image File Name:
8692-66--
1377129548.jpg



MEASUREMENTS

Width: 10	Length: 13.25	Height: 27.75	Extension: 13.25
Height Adjustable: No	Min Overall Height: 0.00	Max Overall Height: 0.00	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 12.10
Canopy Width: 6.63	Canopy Height: 14.63	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 5.00	Center to Bottom: 22.63

LAMPING

No. of Bulbs: 3	Light Type: B10.5 Cand			
Max Bulb Wattage: 60	Socket: E12 Candelabra			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell included:	Lamps included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
	0			

SHADE / GLASS

Description:	Material: Glass
Part No.: G8692A	Quantity: 8
Width:	Height:
	Length:



SHIPPING

Carton Width: 13.000	Carton Height: 31.000	Carton Length: 16.000
Carton Weight: 15.752	Carton Cubit Feet: 3.731	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack: 1



Wet Location

Yes



ETL Intertek

Yes