



## 20A, 125V EXTRA-HARD USE HOSPITAL- GRADE ANGLED PLUG, BLACK & CLEAR

PS5366HGAN | [Pass & Seymour](#)

### FEATURES & BENEFITS

Straight Blade Plug 2pole 3wire 20amp 125v



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Angle plugs and adapters both allow for 4-position face rotation.
- Tri-drive assembly and cord-grip screws are standard on all angle adapters.
- Angle adapter (sold separately as catalog number EHU15AN) will accommodate all Pass & Seymour EHU-style Straight Blade plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Black

Type: Angle devices

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121402

UR: No

## DIMENSIONS

Depth (US): 1.35"

Height (US): 2.13"

Width (US): 1.53"

## TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

