

Item #: **8261-66-L**
UPC Code: **747396092195**
Product Family Name: **Mossoro™**
Finish: **Black**
Category: **Wall Mount**
Category Type: **Outdoor Lighting**
Certification
3187291
Patents

Notes:



Image File Name:
8261-66-L--
1409328754.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
5.75		14.25	7
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	3.53
Canopy Width:	Canopy Height:	Canopy Length:	
5.00	7.00		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		7.75	7.00

LAMPING

No. of Bulbs:	Light Type:			
1	L-Ac10-Md770			
Max Bulb Wattage:	Socket:			
11	Led			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes		30000	N	Yes
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	2700	81	770.000	399.500



SHIPPING

Carton Width:	Carton Height:	Carton Length:
8.630	16.750	9.880
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
4.730	0.826	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
18.000	17.500	20.250
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
21.296		4

SHADE / GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
	4
Width:	Height:
3.75	4.50
	Length:
	4.75

LED

LED

Yes



Wet Location

Yes



ETL Intertek

Yes