



SPECIFICATION SHEET

T12 Timeless, Vintage Inspired Lamp

Item Number **04128**

Specifications

Energy Used (Watts).....	40
Domestic Code	VINTAGE/40/T12
Volts	120
Brightness (Lumens)	N/A
Average Rated Hours	1500
Life (in years)*	1.3
Dimmable	Yes
Filament Type.....	12-Anchor
Estimated Yearly Energy Cost**	\$4.82
Package Type.....	Card, Tray Pack
Country of Origin.....	China



Physical Characteristics

Finish.....	Clear
Base.....	E26 (Medium)
MOL	4.25"

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

© WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.