

Item #
1498-357

Product Family Name:
Nanti

Category:
SEMI FLUSH

Certification
3057374

Patents:

UPC Code:
747396068947

Finish:
Iron Oxide

Category Type:
Semi Flush

Notes:



Image File Name: **1498-357.jpg**



MEASUREMENTS

Width:	Length:	Height:	Extension:
14	14	12.25	
Height	Min Overall	Max Overall	Slope:
Adjustable:	Height:	Height:	No
No			
Wire Length:	Chain Length:	Safety Cable	Net Weight:
7		Included:	8.14
		No	
Canopy Width:	Canopy Height:	Canopy Length:	Center to
4.88	0.75	4.88	Bottom:
Backplate Width:	Backplate	Center to Top:	
	Height:		

LAMPING

No. of Bulbs:	Light Type:			
3	A19 MED			
Max Bulb	Socket:			
Wattage:	E26 MED			
60				
Dimmable:	Ballast:	Rated Life	Photocell	Bulb/LED
Yes		Hours:	Included:	Included:
			No	N
Bulb/LED	Color Temp.:	CRI:	Initial	Delivered
Included:			Lumens:	Lumens:

SHADE / GLASS

Description:	Material:
Etched Vanilla	Glass
Part No.:	Quantity:
G1498-CRV	1
Width:	Height:
11.75	5.5
	Length:



SHIPPING

Carton Width:	Carton Height:	Carton Length:
16.0	8.5	16.0
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
10.516	1.259	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1



**Damp
Location**



Title 17



**ETL
Intertek**



WARNING: Handling this product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. Wash hands with soap and water after installing, handling, cleaning or otherwise touching this product. For more information go to: www.P65Warnings.ca.gov.

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.