



S3860

25G25/SL
25 watt G25 Incandescent; Silver Crown; 1500 average rated hours; 150 lumens; Medium base; 120 volts

Features

- Decorative incandescent
- Long Life
- Brass Base



S3860

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3860	045923038600	25	G25	Medium	E26	25G25/SL	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Silver Crown	4-3/8"	3.13"	C-9	150	1500	72/6	Box

Dimmable/Non-Dimmable	RoHS Compliant
Dimmable	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

