

Monroe Collection
Monroe 5 Light Chandelier NI
43158NI (Brushed Nickel)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Ordering Information

Product ID	43158NI
Finish	Brushed Nickel
Available Finishes	NI, OZ, OZ, NI
Collection	Monroe Collection

Dimensions

Base Backplate	5.75 DIA
Chain/Stem Length	72.00"
Weight	17.30 LBS

Specifications

Material	Steel
Diffuser Description	Satin Etched

Electrical

Voltage	120V
Lead Wire Length	20.00"

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	5
Max or Nominal Watt	100W
Socket Wire	105
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	25.00"
Overall Height	99.00"
Width	27.00"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		