

Item #:	UPC Code:
P4318-084	844349011804
Product Family Name:	Finish:
George's Reading Room™	Brushed Nickel
Category:	Category Type:
Swing Arms	Wall Lamp
Certification	
3057374	
Patents	
Notes:	
On/Off Dimmer	



Image File Name:
P4318-084--
1377187629.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
13.75		6.25	5
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
96		No	3.02
Canopy Width:	Canopy Height:	Canopy Length:	
5	6.25		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		3.13	3.13

SHADE / GLASS

Description:		Material:
		Alum Casting
Part No.:		Quantity:
		1
Width:	Height:	Length:
2.63	1.13	3.5

LAMPING

No. of Bulbs:	Light Type:			
1	L-L8-Md590			
Max Bulb Wattage:	Socket:			
8	Led			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes		30000		Yes
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	3000	84	590	438.76



SHIPPING

Carton Width:	Carton Height:	Carton Length:
4.5	8	22
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
4.05	0.458	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
9.5	16.75	22.5
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
16.896		4

LED

LED

Yes



Title 17

Yes



ETL Intertek

Yes