



SURECRIMP® ALND ALUM 2 HOLE LONG BARREL



- Manufactured from high strength aluminum alloy which offers maximum conductivity and excellent crimping characteristics.
- Electro-Tin plated for low contact resistance.
- Chamfered entry for easy conductor insertion.
- Color coded end cap identifies the proper compression die.
- Roll marked barrel for easy identification and proper location of crimps.
- Pre-filled with DE-OX prevents oxide from forming.
- Dual rated for Aluminum or Copper conductors.
- UL 486A/B 90° C Listed and CSA Certified.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size applicable when installed with specified dieless tools.
- UL File E6207

Item ID	Conductor Size	Expanded Conductor	Bolt/Stud Size	Mounting Hole	Mounting Hole	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog	Outside Diameter	Inside Diameter	Standard Package	NAED/UPC Number
ALND-250-12-134	250 kcmil	250kcmil - 1/0 AWG	1/2	0.5620	1-3/4	3.0420	1.2640	1.5350	1.5975	5.4000	RED	324	ILD-324	0.9240	0.5950	5	0783669687408