



BURNDY Catalog Number
UPC Number
Description
Status

GAR2026
7818102364066
4-2/0CU 3IPS
Active

Web Use
BURNDY Product Line

Dimensional

Width (in) 4.81
Length (in) 1.56
Height (in) 5.62
Size (Hex) or Size (Bolt) 3/8
Size (Hex) or Size (Bolt) - in 0.38
B Length (in) 3.50
Width (Fraction) 4-3/4
Height (Fraction) (in) 5-5/8

General

Product Description

Mechanical Grounding Connector,
Cable to Rod or Pipe, 4 AWG
(Sol)-2/0 AWG (Str), 3" Pipe,
3"-3-1/2" Rod, Bright Dipped

Other

Type of U Bolt

267

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards
Rated for Direct Burial

Y
Y
Exempt
N
N
UL467
Y

Conductor(s)

Copper Tube Size (SCH40) - Range 3 IPS IPS
Rod Size (Range) 3 in-3 1/2 in
Copper Solid Size (Range) 4 AWG-3/0 AWG
Copper Stranded (Range) 5 AWG-2/0 AWG
Rebar Size (Range) N/A

Physical

Type of Hardware
Installation Torque
Type of Plating
Plated (Yes or No)
Product Material

DURIUM® Silicon Bronze
240
Bright Dipped
N
Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175