

## FM272ORB: 2 - Light Indoor Flush Mount



### Dimensions:

**Diameter:** 14" **Wire:** 8"  
**Height:** 5 1/4"  
**Weight:** 11.5 lbs.

### Bulbs:

2 - Medium A19 60w Max. 120v - Not included

### Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
- 

### Material List:

1 Body - Steel - White

### Safety Listing:

Safety Listed for Dry Locations  
 Safety Listed for Dry Locations

### Instruction Sheets:

English (FM272)

**Collection:** Barrington

**UPC #:** 014817330830

**Finish:** Oil Rubbed Bronze (ORB)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Etched Glass	Opal Etched	1				3 1/2	12 1/4				

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Mounting Plate	1	4				

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	FM272ORB	1	014817330830	17	16.5	8.5	1.38	9.68	125	Yes

Master Pack	FM272ORB	2	10014817330837	17.5	17.25	18	3.145	19.48	125	Yes
NJ Pallet		32		48	40	72	80	320		No
NV Pallet		32		48	40	74	82.222	285		No