

Catalog Number: TY5354M
Product ID: 7TAG009520R0066
UPC Number: 78621088637
EAN Number: 05414363066132
Status: Active



Actual

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 371.35mm (14.62 Inches), Width of 4.83mm (0.19 Inches), Thickness of 1.4mm (0.055 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), #10 Screw for Mounting

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5037 Cable Ties & Wraps
Brand Name	Ty-Rap
Type	Mounting Head
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Width	0.19 Inches/4.83mm
Length	14.62 Inches/371.35mm
Thickness	0.055 Inches/1.4mm
Bundle Diameter	to 4.0 Inches/101.6mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Double Locking Head
Tensile Strength	50 Pounds/222 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.83mm
Length belt/tape/tie	371.35mm
Tie thickness	1.4mm
Min. holding force	222N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	17x5.8x5.8
Weight Uom	10 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com