

# GENERATION LIGHTING

## 88200-12: One Light Outdoor Wall Lantern



### Dimensions:

**Width:** 6 1/4"                      **Extends:** 10"  
**Height:** 19 3/4"                    **Wire:** 6 1/2"  
**Weight:** 4.6 lbs.                    **Mounting Proc.:** Cap Nuts  
**Connection:** Mounted To Box

### Bulbs:

1 - Medium A19 100w Max. 120v - Not included

### Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

1 Body - Die Cast Aluminum - Black

### Safety Listing:

Safety Listed for Wet Locations

### Instruction Sheets:

English (HC-280)  
French (HC-280 F)

**Collection:** Wynfield

Black Cast Aluminum Single Light Outdoor Wall Lantern with Clear Beveled Glass

One Light Wall Lantern in Black Finish

**UPC #:** 785652882005

**Finish:** Black (12)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Beveled	3	G501188-631								
Panel	Glass	Clear Beveled	3	G501188-631								

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	9	5	1		15 1/4	

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	88200-12	1	785652882005	12	8.5	16	0.944	5.8	125	Yes
NJ Pallet		64		48	40	70	77.778	371		No
NV Pallet		64		48	40	70	77.778	371		No