



GE  
Lighting

### 82345 - Remote 3ft LED Plastic Tubes

#### LED18T8/3/840

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ Each LED tube is operated by a GE Lighttech™ driver.
- ☞ 66% longer life than LFL (50,000 vs. 30,000 hours)
- ☞ Instant on light
- ☞ NSF Rated for food application (shatter resistant)
- ☞ Easy disposal, non-hazardous waste
- ☞ UL Listed

#### Product Photo



#### CAUTIONS & WARNINGS

##### Caution

Risk of electric shock

Suitable for damp locations

Not intended for use with emergency exit fixtures or emergency exit lights

#### GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	50000 h
LED Tube Type	Plastic
10 Digit U	4316882345
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Carton, Sleeve
Estimated Energy Cost per Year	1.81
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	1800 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

#### PRODUCT INFORMATION

Product Code	82345
Description	LED18T8/3/840
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168823456
Standard Package GTIN	00043168823456
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168823456
Alternative Unit Of Measure	CASE
Standard Package Quantity	10
Ean UPC	043168823456
Standard Package GTIN	10043168823453
No Of Items Per Sales Unit	10
No Of Items Per Standard Package	10
Sales Unit	Case
UCC	043168823456

#### DIMENSIONS

Bulb Max Overall Length-MOL	36.0 in
-----------------------------	---------

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	16 W
---------------------	------