



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5881-31WB

Non-Metallic

One-light polycarbonate lantern with white acrylic diffuser. Energy Star.
CFL Bulb included.

Category: Outdoor

Finish: Black (painted)

Construction: Polypropylene construction

Glass: White acrylic diffuser



Width: 6"
Height: 8-7/8"
Depth: 6-7/8"
H/CTR: 4-1/8"

Glass: 5" dia.
Height: 5-5/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 4-7/16" W., 5-1/4"	Pre-wired 6" of wire supplied 120V	Quantity: 1 18W GU-24 (included) GU24 plastic socket	UL-CUL Wet location listed 1 year warranty Companion fixtures are available 