



Actual

Catalog Number: TC5357
Product ID: 7TAG009870R0006
UPC Number: 78621080641
EAN Number: 05414363059080
Status: Active

Heavy-Duty Mounting Cradle, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius, Weather and Ultraviolet Resistant, Length of 44.45mm (1.75 Inches), Width of 19.1 (0.75 Inches), Height of 15.9mm (0.626 Inches), for Use with Lashing Ties, Screw Mounting Method, 0.25 Inch Screw

- Weather-resistant nylon mounting base for use with lashing ties Cat. No. Ty-5409 (.500 wide).

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Heavy Duty Application
Special Features	Weather-resistant nylon mounting base for use with lashing ties Cat. No. Ty-5409 (.500 wide).
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Screw
Operating Temperature	-40 Degree F to 185 Degree F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	44.45mm
Width	19.1mm
Height	15.9mm
Suitable for cable tie width to	12.7mm
Type of fastening	Other
Diameter mounting hole	6.7mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Black

Packaging

Inner Quantity	25
Outer Quantity	250
Outer Dimensions (inches)	9.2x9.3x4.8
Weight Uom	1.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com