



BURNDY Catalog Number
UPC Number
Description
Status

YA36L11
 7818102503966
 CULUG-600 KCMIL-1/2 STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.29
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.27
B Length (in)	1.38
Pad Width (in)	1.74
Strip Length	1-3/4

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 600 kcmil, 1/2" Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	600 kcmil

Physical

Type of Plating	Tin - Electro Plated
Color Code	Green
Plated (Yes or No)	Y
Index Number	22,472
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175