



Actual

Catalog Number: H 122 3/8 EG
Product ID: 7TAA004110R0007
UPC Number: 78599104419
Status: Active

Strut Fastener, Size 3/8 Inch, Electro-Galvanized Steel

- Fewer parts, less installation time..results - Labor Savings!
- Precision threads trap the threaded rod for a sturdy hold that can be adjusted up or down for fine-tune positioning.
- Functions as a hex nut, square washer, and flat washer combined.
- Locking pin holds it in the desired position
- Sturdy steel construction that is load bearing.

North American Specifications (UNSPSC)

UNSPSC	39121701 Electrical hangers
IGCC	5026 Electrical hangers
Brand Name	Kindorf
Type	Fittings & Hardware
Special Features	Fewer parts, less installation time..results - Labor Savings!
Application	For use with Kindorf channels.
Size	3/8 Inch
Thickness	0.380 Inch
Material	Steel
Finish	SilverGalv

European Specifications (ETIM)

ETIM	EC000482 Mounting element for support/profile rail
Suitable for	U-profile
Model	Other
With screw accessories	N
Material	Steel
Material quality	Other
Surface protection	Galvanic/electrolytic zinc plated

Packaging

Outer Quantity	50
Outer Dimensions (inches)	8.37x4.5x3.75
Weight Uom	19.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000524

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com