



## FED SPEC GRADE USB CHARGER W/ TAMPER-RESISTANT 20A DUPLEX RECEPTACLES, BROWN

TR5362USB | [Pass & Seymour](#)

### FEATURES & BENEFITS

Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- **Overall 3.1A USB charging capability:** Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.
- **AC receptacles available in 15 and 20A, 125V.**
- **AC receptacles are tamper-resistant as standard**—patented shutter system prevents improper insertion of foreign objects.
- **Multiple color** options available.
- **Back and side wire terminals** accommodate #14 AWG - #10 AWG stranded and solid copper wire.
- **Stainless steel** auto-ground clips assure positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown

Available Colors: Black, Gray, Green, Ivory, Light Almond, Nickel, Red, White

Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42, C22.2 No. 223

CSA Standard: Yes

cULus: Yes

Federal Spec: Yes  
UL Listing No: Complies with test requirements UL498, UL1310  
UL Standard: Yes

#### **DIMENSIONS**

Depth (US): 1.392"  
Height (US): 3.28"  
Width (US): 1.693"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20R  
NEMA Rating: Yes  
Volts: 125V

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA