



Powering Business Worldwide

pe.eaton.com

Definite Purpose Control - Contactor

C25DNF330T

UPC:782116311422

Dimensions:

- **Height:** 3 IN
- **Length:** 3.35 IN
- **Width:** 2.4 IN

Weight:.9 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Quick
- **Amperage Rating:** 30A
- **Coil:** 24 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Resistive Load:** 40A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - C25DNF330T](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

