



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. Type: HBL  
Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240V Amperage Rating: 20A Trip Range: Thermal Magnetic Interrupt Rating: 65 AIC Number Of Poles: 2P

|                                |                         |
|--------------------------------|-------------------------|
| Number of poles                | 2                       |
| Suitability for operation      | Electrical Distribution |
| Electricity                    |                         |
| Continuous current rated value | 20 A                    |
| Model                          |                         |
| product brandname              | SIEMENS                 |
| Type of electrical connection  | BOLT-ON                 |
| Mechanical Design              |                         |
| Depth [in]                     | 3 in                    |
| Design of the product          | HBL                     |
| Height [in]                    | 2 in                    |
| Width [in]                     | 3 in                    |
| General product approval       |                         |
| Standard                       | UL 489                  |
| last modified:                 | 08/20/2017              |