



*Hoffman*

## Temperature Control Switch - Normally Open

Catalog Number: ATEMNO  
US List Price (USD): \$68.61



### Model Code:

- 71170

### Bulletin Number:

- D85

### Industry Standards:

cURus; File No. E164102 UL94-V0 Protection rating IEC IP30 CSA Certified, File Number 215952 CE

## Description

---

### Applications:

These easy-to-install thermostats regulate and monitor air temperature in enclosures that contain heat-emitting equipment. Thermostats prolong heater and fan life expectancy by controlling operation time and increase electrical component working efficiency by exposing them to fewer environmental contaminants.

### Features:

- Additional label for conversion to Celsius scale and blank label to cover set point range label when adjustment after initial setting is not desired are included
- Bimetal temperature sensor
- Plastic housing
- Connections consist of tubular screw terminals for AWG 14 (.04 sq. in.)
- Provision for both panel mounting and DIN rail mounting

### Finish:

Molded plastic housing is black

### Notes:

Reference the Spec Sheet in the Downloads tab for complete product specifications.

Technical Data

---

Temperature Control Switch - Normally Open

Catalog Number	<a href="#">ATEMNO</a>
Description	Temperature Control Switch - Normally Open
Height (in.)	2.37
Width (in.)	1.31
Depth (in.)	1.55

Certifications

---



EU Certification

Documents

---



3D STEP CAD



Temperature Control Switch CADFiles



Temperature Controlls Instruction Manual



Spec Sheet



2D DXF CAD



Spec Sheet



Temperature Controlls Instruction Manual



Temperature Control Switch CADFiles

No accessories available.