



S9156

0.5W C7/CL/LED/120V/CD
0.5 watt LED; C7; Clear; 2700K; Candelabra base; 120 volts

Features

- Solid State LED lighting
- Candle shaped specialty lamp
- Long life
- Carded
- Wet location



S9156

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	
S9156	045923091568	120	0.5	C7	Candelabra	E12	0.5W C7/CL/LED/120V/CD	
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	
Non-Dimmable	Clear	2-3/32"	0.88"	14	25000	2700	Warm White	
CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification		Warranty
80	360	12/48	CD/1	Yes	Yes	cULus - Wet Location Rated		3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

