

## A-Type 2700K, 480 lumens, 40w Replacement, Dimmable

- ENERGY STAR qualified, ideal replacement for standard incandescent or CFL bulbs
- Energy efficient, long-lasting LED – over 80% reduction in energy costs compared to incandescent bulbs
- Warm white light – similar to incandescent
- Compatible with most commercial dimmers\*
- Instant-on – full illumination with the flip of a switch
- Shatter-resistant bulb surface
- Environmentally friendly – Contains no mercury
- 25,000 hour lifetime – 22.8 years!\*\*
- 5-year limited warranty

\* Dimming range may vary based on dimmer used.

\*\* Based on 3 hours average daily use.



### Specifications

Lamp Type	A-Type, 2700K, 480lm - Dimmable
Part Number	98781
Model	A-L480-C27-B220-D
Dimmable	Yes
Voltage	120V
Wattage	7W
Color Temperature	2700K
Lumen Output	480 lm
Efficacy	68lm/W
CRI	80
Beam Angle	220°
Operating Temperature	-20°C to 40°C
Socket	E26
Design life	25,000 Hrs.
Dimensions(L x W x H)	2.40 x 2.40 x 4.40 in
Weight	3 oz.

### Certifications:



**A-Type 2700K, 480 lumens, 40w Replacement,  
Dimmable**

**Additional Images:**

