

Monroe Collection  
Monroe 5 Light 27" Chandelier - Sterling Gold  
SGD  
43158SGD



Dimensions

|                |        |
|----------------|--------|
| Height         | 25.00" |
| Overall Height | 99.00" |
| Width          | 27.00" |

Alternate Lamps

| Lamp Included | Bulb Listing | Light Source | Max Wattage/Range | Bulb Product ID | Dimming |
|---------------|--------------|--------------|-------------------|-----------------|---------|
| No            | Hybrid       | CFL          | 23-30W            |                 |         |

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_

Ordering Information

|                    |                   |
|--------------------|-------------------|
| Product ID         | 43158SGD          |
| Available Finishes | OZ, NI, OZ, NI    |
| Collection         | Monroe Collection |

Dimensions

|                   |           |
|-------------------|-----------|
| Base Backplate    | 5.75 DIA  |
| Chain/Stem Length | 72.00"    |
| Weight            | 17.30 LBS |

Specifications

|                   |              |
|-------------------|--------------|
| Material          | Steel        |
| Glass Description | Satin Etched |

Electrical

|                  |        |
|------------------|--------|
| Voltage          | 120V   |
| Lead Wire Length | 20.00" |

Qualifications

|              |  |
|--------------|--|
| Safety Rated | Dry  |
| Warranty     | <a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a> |

Primary Lamping

|                       |              |
|-----------------------|--------------|
| Light Source          | Incandescent |
| Lamp Included         | Not Included |
| Number of Lights/LEDs | 5            |
| Max or Nominal Watt   | 100W         |
| Socket Wire           | 105          |
| Socket Type           | Medium       |
| Lamp Type             | A19          |