



Actual

**Catalog Number:** GUAX26-G  
**Product ID:** 7TAA087360R0013  
**UPC Number:** 70450838639  
**Status:** Active

PVC Double-Coated Conduit Outlet Box for Hazardous Locations, GUAX Type - X Shape, Pipe Size 3/4 Inch/21 Metric, Box is Ductile Iron with Zinc Plating, Cover is Die Cast Aluminum, Cover Opening 3.00 Inch/76.20 Millimeters, Gray

- Grade 60-45-10 ductile iron bodies and cast aluminum covers
- Nominal .002 inch (2 mil) blue urethane coating on both interior and exterior and nominal .040 inch (40 mil) PVC coating bonded to exterior
- All hubs have a minimum of five full threads, integral bushing and pressure-sealing sleeves
- All units furnished with internal grounding screw and ship complete with aluminum cover with O-ring gasket
- Explosion-proof, dust-ignition-proof, raintight and suitable for use in the following environments. Class I, Division 1 & 2, Groups C & D - Class II, Division 1, Groups E, F, G - Class III, Division 1 & 2 - NEMA 3, 4, 7 CD, 9 EFG.
- Provide access to conductors for maintenance and future system changes
- Mounting outlets for fixtures, with proper covers
- To change direction in rigid conduit systems
- Join two or more pieces of conduit long runs

#### North American Specifications (UNSPSC)

UNSPSC	39121331 Hazardous location box
IGCC	4485 Hazardous location box
Brand Name	Ocal
Type	GUAX Type Hazardous Location Outlet Box, PVC Coated
Special Features	O-Ring Gasket Provided to Assure NEMA 4 Rating
Application	For Use in Hazardous Locations to Provide Access to Conductors for Pulling, Splicing, Maintenance and Future Changes/upgrades
Material	Zinc Plated Iron Body with Aluminum Cover
Size	3/4 Inch/21mm
Color	Gray
Cubic Capacity	13.3 Cubic Inches

#### European Specifications (ETIM)

ETIM	EC002600 Box/housing for surface mounting on the wall/ceiling
Shape	Rectangular
For tubediameter	Other
Number of inlets	4
Type of housing feed-through	Thread
Material	Other
Surface protection	Other
Colour	Grey

#### Packaging

Inner Dimensions (inches)	xx
Outer Quantity	12
Outer Dimensions (inches)	16.25x13.75x7.25
Weight Uom	3.87 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

### For further technical assistance, please contact us...

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)