



GE
Lighting

14075 - null

LED13DA21/827

Product Photo



GENERAL CHARACTERISTICS

Primary Application	General Purpose
Product Technology	LED
Rated Life (Hours)	25000 h
10 Digit U	4316814075
Lamp Count	1
Life in Years	22.8 yr
Requested Structure	Carton
Estimated Energy Cost per Year	1.57
Base	E26

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	85
Initial Lumens-nominal	1100 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	14075
Description	LED13DA21/827
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168140751
Standard Package GTIN	00043168140751
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168140751
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168140751
Standard Package GTIN	10043168140758
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168140751

DIMENSIONS

Bulb Max Overall Length-MOL	5.28 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V