

Print



## F32T8/830/ECO 109398 F32 T8 3000K 85CRI ECO PROLUME

Product Number: **109398**  
 UPC: 807154193981

This product can not be shipped to California addresses, pursuant to the Title 20 California Appliance Efficiency Regulation. See [www.energy.ca.gov/title20](http://www.energy.ca.gov/title20) for details.

Log In for Price and Availability

Note: this product is only sold in multiples of 25 items

Specifications	Resources	Technical	
Applications	Paint stores, hair salons, retail stores and print shops		
Average Life (Hrs)	24000		
Base	Medium Bi-Pin		
Brand	ProLume Eco-Shield		
Bulb	T8		
CRI	86		
Color Temperature	3000		
Cross Reference - Osram Sylvania	FO32/830/ECO		
Design Lumens	2900		
Dimmable	No		
HTS code	8539310040		
Initial Lumens	3050		
Input Frequency (Hz)	60		
Markets	Residential, Commercial		
Master Carton Quantity	25		
Maximum Overall Diameter	1		
Maximum Overall Length	48		
Nominal Length	48		
Operating Position	Universal		
Prod Code	F32T8/830/ECO		
Product Category	Linear Fluorescent		
Product Description	F32 T8 3000K 85CRI ECO PROLUME		
Product Number	<b>109398</b>		
SS BUY PKG	25		
Start Type	Instant/Programmed Start		
Warranty (Yrs)	2; 3 When Installed with ProLume Ballast		
Wattage (W)	32		

### Products

#### Lamps



#### Ballasts



#### Luminaires



### Resources

Catalogs  
 Sell Sheets

### Contact Us

Corporate Office:  
 Halco Lighting Technology  
 2940 Pacific Drive  
 Norcross, GA 30071  
 Toll Free: 800.677.3334  
 Office: 770.242.3612  
 Fax: 800.880.0822  
 Email: [customer care@halco](mailto:customer care@halco)

