

Item #: **73093-189**  
UPC Code: **747396090887**  
Product Family Name: **Willow Pointe**  
Finish: **Chelesa Bronze™**  
Category: **Wall Mount**  
Category Type: **Outdoor Lighting**  
Certification: **4006752**  
Patents

Notes:



Image File Name:  
73093-189--  
1403255067.jpg



## MEASUREMENTS

|                    |                     |                        |                   |
|--------------------|---------------------|------------------------|-------------------|
| Width:             | Length:             | Height:                | Extension:        |
| <b>11</b>          |                     | <b>22</b>              | <b>8.75</b>       |
| Height Adjustable: | Min Overall Height: | Max Overall Height:    | Slope:            |
| <b>No</b>          |                     |                        | <b>No</b>         |
| Wire Length:       | Chain Length:       | Safety Cable Included: | Net Weight        |
| <b>7</b>           |                     | <b>No</b>              | <b>8.42</b>       |
| Canopy Width:      | Canopy Height:      | Canopy Length:         |                   |
| <b>4.63</b>        | <b>9.00</b>         |                        |                   |
| Backplate Width:   | Backplate Height:   | Center to Top:         | Center to Bottom: |
|                    |                     | <b>9.75</b>            | <b>11.88</b>      |

## LAMPING

|                   |                          |                   |                     |                   |
|-------------------|--------------------------|-------------------|---------------------|-------------------|
| No. of Bulbs:     | Light Type:              |                   |                     |                   |
| <b>4</b>          | <b>B10.5, Candelabra</b> |                   |                     |                   |
| Max Bulb Wattage: | Socket:                  |                   |                     |                   |
| <b>60</b>         | <b>E12, Candelabra</b>   |                   |                     |                   |
| Dimmable:         | Ballast:                 | Rated Life Hours: | Photocell Included: | Lamps Included:   |
| <b>No</b>         |                          |                   | <b>N</b>            | <b>No</b>         |
| Lamp Included:    | Color Temp.:             | CRI:              | Initial Lumens:     | Delivered Lumens: |
| <b>No</b>         |                          |                   |                     |                   |



## SHIPPING

|                     |                     |                          |
|---------------------|---------------------|--------------------------|
| Carton Width:       | Carton Height:      | Carton Length:           |
| <b>11.000</b>       | <b>19.750</b>       | <b>15.250</b>            |
| Carton Weight:      | Carton Cubic Feet:  | Small Package Shippable: |
| <b>10.274</b>       | <b>1.917</b>        | <b>Yes</b>               |
| Master Pack Width:  | Master Pack Height: | Master Pack Length:      |
|                     |                     |                          |
| Master Pack Weight: | Master Cubic Feet:  | Multi-Pack:              |
|                     |                     | <b>1</b>                 |

## SHADE / GLASS

|               |              |
|---------------|--------------|
| Description:  | Material:    |
|               | <b>Glass</b> |
| Part No.:     | Quantity:    |
| <b>G73093</b> |              |
| Width:        | Height:      |
| <b>8.63</b>   | <b>8.88</b>  |
|               | Length:      |



Wet Location

Yes



ETL Intertek

Yes