



Actual

Catalog Number: CLNPL1-G
Product ID: 7TAA087160R0000
UPC Number: 70450836169
EAN Number: 05415022251272
Status: Active

Urethane Coated Conduit Nipple Fitting, 1 Inch/27 Metric Pipe Size x Close, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Brand Name	Ocal
Type	Conduit Fittings-PVC Coated
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings
Standard	cULus E46453, CSA, RoHS
Material	Steel
Color	Gray
Finish	PVC Coated
Length	Close
Trade Size	1 Inch/27 Metric

European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	27
Material housing	Other
Surface protection	Hot dip galvanized
Model	Straight

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	25
Outer Dimensions (inches)	8.25x6.5x5.25
Weight Uom	15 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com