



Job Name:		Item Number:	
Specifier Name:		Sales Agency:	
Specifier Contact:		Agency Contact:	
Fixture Type:		Comments:	
Quantity:		Approval:	

40' Reel High Output LED Tape 2700K



Description

Specifications

Item Number	98708S-15
Finish	White
Dimensions	L: 480" W: 9/16" H: 3/16"
Voltage	24V
Light Source	LED
Color Temperature	2700°K
Lumens	16,000
Watts Consumed	220 watts
Efficacy	72.7 lm/w
Color Rendering	>80 CRI
Rated Average Life	50,000 hours to 70%
Safety Listing	cETL Listed for Wet Locations
Warranty	5-Year Limited Warranty

Instruction Sheets

- Trilingual (English, Spanish, and French) (990LXTAPE)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	98708S-15	1	785652252693	14	14	1	0.113	2.1	Yes
Master Pack	98708S-15	6	10785652252690	13.78	13.78	5.2	0.571		Yes
Shipping Master	98708S-15	12	20785652252697	14	11.2	15.4	1.397	27.7	Yes