

Product Specifications

Project _____

Location _____

Type _____

12014

Manufactured by Kichler® Lighting



DESCRIPTION

Task Work Direct Wire 120V Xenon -

A cost effective and easy to install undercabinet lighting option.

SPECIFICATIONS

MATERIALS:

Housing: Steel

Lens: Frosted Glass

FINISHES: Painted Bronze, Silver or White

DIMENSIONS:

Length: 30.00"

Width: 5.00"

Height: 1.25"

LIGHT SOURCE:

- 4 – 20W Xenon Lamp
- 2650K Color Temperature
- 100 Color Rendering Index (CRI)
- 2500 hour expected life span

ELECTRICAL DATA:

Input Voltage: 120V AC

Power Consumed: 80 watts

Efficacy: 5 lumens/watt

FEATURES

- C-UL Listed for Cabinet Use – UL Standard No. 2108
- 1/2" Trade Size Knockout
- Large Wire Compartments
- Intended for Direct Wire Connection Through NM/BX Cable Connector (Included)
- High/Low, On-Off Switch
- Bulb(s) Included
- Cord and Plug Accessory Available

PHOTOMETRIC DATA

Countertop Foot-Candle Measurements Available Upon Request.

FOOT-CANDLE MEASUREMENT ON WORK SURFACE

A	LIGHT OUTPUT FC (COUNTER FRONT)	15.0
B	LIGHT OUTPUT FC (COUNTER MIDDLE)	33.6
C	LIGHT OUTPUT FC (COUNTER BACK)	57.1
D	LIGHT OUTPUT FC (COUNTER WALL)	25.0

