



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
8.00"	13.50"	9.00"
<u>BP Height</u>	<u>BP Width</u>	
5.25"	5.25"	
<u>Hanging Weight</u>		
3.31 lb		

Lamping:

Incandescent MB	2,300 Rated Lumens
2.00 60W MB	Color Temperature
120 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
4.08 lb	8.86"	10.63"	11.61"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209212114	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Wilshire WS

Material:

Steel

Certification:

Damp Location  
Location

Additional:

MB (Not Included)  
Lighting Direction: Both