



Measurements:

<u>Height</u>	<u>Width</u>	
9.00"	13.00"	
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>
6.92 lb	5.00"	1.00"

Lamping:

Incandescent MB	1,344 Rated Lumens
2.00 60W MB	Color Temperature
120 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
9.90 lb	16.14"	9.06"	16.14"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209058460	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location  
Location

Additional:

MB (Not Included)