



**Measurements:**

<u>Height</u>	<u>Width</u>		
30.00"	31.50"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
22.66 lb	5.00"	1.00"	5.00"

**Lamping:**

Incandescent MB Incandescent 10,350 Rated Lumens  
 9.00 100W MB Incandescent Color Temperature  
 900 total watt 2,500 Rated Life  
 Dimmable : Standard

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
30.15 lb	29.50"	11.75"	31.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209058392	Yes	

**Finish:**

Oil Rubbed Bronze OI

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location  
 Location

**Additional:**

MB Incandescent (Not Included)