



*height from center of outlet to the top of the fixture

Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
19.50"	8.00"	9.50"
<u>BP Height</u>	<u>BP Width</u>	<u>HCO</u>
10.50"	5.00"	11.50"
<u>Hanging Weight</u>		
4.58 lb		

Lamping:

Incandescent MB	1,150 Rated Lumens
1.00 60W MB	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.78 lb	10.04"	28.94"	13.98"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209302303	Yes	

Finish:

Bronze BZ

Glass:

Seedy CD

Material:

Die Cast Aluminum

Certification:

Wet Location
Location

Additional:

MB (Not Included)