



Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>
26.00"	12.75"	12.75"
<u>Hanging Weight</u>		
7.28 lb		

Lamping:

Incandescent CA E12	0 Rated Lumens
3.00 60W CA E12	Color Temperature
180 total watt	
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
9.11 lb	14.76"	15.94"	14.76"
<u>Master Pack Qty</u>			
1.0000	783209119055	Yes	
<u>UPC</u>			

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location

Additional:

CA E12 (Not Included)