

DESCRIPTION

The CEW Series offers quality and value with a wet location rated emergency Exit sign. Housing and face-plate made from impact resistant UV stabilized polycarbonate. Housing is corrosion resistant and face-plate is fully gasketed. Exit face illumination by low energy, long-life red or green ultra bright LED's. The Exit letters measure 6" with a red or green diffuser. Single-face models can be wall mounted by use of molded-in template, end or ceiling mounted. Double-face models are end or ceiling mounted only. Includes canopy and universal mounting plate. Water-proof test switch and AC-on indicator located at Exit bottom. Directional indication made by place-able chevrons. Conduit entry KO's located in top and side housing, with conduit fitting included.

APPLICATION

The CEW Series can be applied in areas that are susceptible to rain or wet conditions like pool areas or water treatment facilities.

STANDARDS, CERTIFICATION, AND COMPLIANCE

UL924 Listed for Wet Location NFPA 101 and NFPA 70 OSHA CEC T20 Compliant

WARRANTY

2 year full unit warranty



FEATURES

- LED life-cycle of more than 10 years
- Dual-voltage 120 or 277V AC input
- Emergency models include long-life 4.8VDC Nickel Cadmium battery for UL recognized 90 minute operation
- Wet Location Listed(-20°C to 50°C)
- Provided with test switch and AC-On indicator
- · Canopy Included
- 24hr. Re-charge


ENERGY CONSUMPTION

| 120 VAC | 277 VAC |
|---------|---------|
| 2.7 W | 2.7 W |

ORDERING GUIDE

| Catalog Number | Description |
|----------------|---|
| CEWSRE | Wet Location, Single-Face, Red, Emergency |
| CEWDRE | Wet Location, Double-Face, Red, Emergency |
| CEWSGE | Wet Location, Single-Face, Green, Emergency |
| CEWDGE | Wet Location, Double-Face, Green, Emergency |

DIMENSIONS





Single Carton Weight: 4.3 lbs. Master Carton Quantity: 6 each

