



77660-839: Two Light Semi-Flush Convertible Pendant Dimensions:



Diameter: 14 1/4"

Height: 14"

Weight: 7.9 lbs.

Height Flush: 12"

Overall Height: 136 1/2"

Wire: 144" (color/Black)

Chain: 120"

Mounting Proc.: Dual Mount

Connection: Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Collection: Winnetka

Semi-Flush Convertible Fixture in Blacksmith Finish with Satin Etched Glass Shade

UPC #:785652756658

Finish: Blacksmith (839)

Material List:

1 Body - Steel - Blacksmith

1 Chain - Steel - Blacksmith

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

English (HC-1439)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	1					11 13/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 7/16	6		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	77660-839	1	785652756658	15.5	15.5	11.25	1.564	9.9	125	Yes
NJ Pallet		40		48	40	67	74.444	396		No
NV Pallet		40		48	40	67	74.444	396		No