

2" Malleable Iron Rigid Threaded Type LR Conduit Bodies

Item No. LR6M



Topaz's Malleable Iron Rigid Threaded type LR Conduit Body is constructed to offer unmatched high tensile strength and ductility. Strong and resilient malleable iron fabrication is resistant to damage from corrosion and impact. LR type conduit bodies permit 90° right bends

Roomy interior allows for maximum wiring space, smooth, rounded integral bushings in hubs offers protection for conductor insulation. Available in 1/2" to 4" sizes; UL listed.



SPECIFICATIONS

Base Unit of Measure: PCS

Item UPC/EAN Number: 751338213906

Label Description: RIGID CONDUIT BODY- LR TYPE

Label Description 2: THREADED

Label Description 3: MALLEABLE IRON

DESCRIPTION

See description above

Size: 2"
