



GE
Lighting

42133 - null

LED12DP30RW82725

Product Photo



GENERAL CHARACTERISTICS

Primary Application	Track & Recessed
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	25 deg
Center Beam Candle Pwr Candela	4700 cd
Nominal Initial Lumen per Watt	83.3
Rated Beam Spread	25 deg
Initial Lumens-nominal	1000 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	42133
Description	LED12DP30RW82725
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168421331
Standard Package GTIN	00043168421331
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168421331
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168421331
Standard Package GTIN	10043168421338
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168421331

DIMENSIONS

Bulb Max Overall Length-MOL	3.74 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V